

TECHNICAL DATA SHEET

Part No. 111-00290
Article No. 111-00290
Type MBT14SFC



HellermannTyton's MBT Ties are fabricated from corrosion-resistant 316 stainless steel and have a protective polyester coating. Stainless tie design includes a non-releasable locking feature for secure applications. Polyester coating provides smooth edges to make it safer for installers' hands and eliminates contact corrosion between dissimilar materials.

Material	Stainless Steel (SS316L), Polyester (SP)
Operating Temperature	-112°F to +1000°F (-80°C to +538°C)
Flammability	Non-burning (except coating), low smoke in accordance with CSA C22.2 No. 62275:21
Halogen Free	Yes
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	100
Carton Qty.	4000
Customs Number	7326908695

Length (imperial)	14.3 "
Length (metric)	362 mm
Max. Bundle Diameter (imperial)	4.02 "
Max. Bundle Diameter (metric)	102 mm
Min. Tensile Strength (imperial)	121 lbs
Min. Tensile Strength (metric)	540 N
Thickness (imperial)	0.01 "
Thickness (metric)	0.38 mm
Width (imperial)	0.18 "
Width (metric)	4.6 mm

