

# TECHNICAL DATA SHEET

**Part No.** 111-01459  
**Article No.** 111-01459  
**Type** T30R



HellermannTyton T-Series cable ties feature inside serrations providing a positive hold onto wire and cable bundles. The head design guarantees high tensile strength, as well as a low insertion force. The bent tail design allows quick and simple installations by hand. For high volume applications, tensioning tools are available to ensure consistent and safe installation.

<b>Material</b>	Polyamide 4.6 (PA46)
<b>Operating Temperature</b>	-40°F to +266°F (-40°C to +130°C)
<b>Flammability</b>	UL 94 V-2
<b>UV Resistant</b>	No
<b>Use Conditions</b>	For Indoor Use Only
<b>Color</b>	Gray (GY)
<b>Pkg. Qty.</b>	1000
<b>Carton Qty.</b>	5000
<b>Customs Number</b>	3926909988

<b>Cable Tie Head Length (imperial)</b>	0.23 "
<b>Cable Tie Head Length (metric)</b>	5.9 mm
<b>Cable Tie Head Width (imperial)</b>	0.24 "
<b>Cable Tie Head Width (metric)</b>	6.0 mm
<b>Height (imperial)</b>	0.17 "
<b>Height (metric)</b>	4.28 mm
<b>Length (imperial)</b>	5.83 "
<b>Length (metric)</b>	148.0 mm
<b>Max. Bundle Diameter (imperial)</b>	1.38 "
<b>Max. Bundle Diameter (metric)</b>	35.0 mm
<b>Min. Tensile Strength (imperial)</b>	30 lbs
<b>Min. Tensile Strength (metric)</b>	135 N
<b>Serration Side</b>	Inside Serrated
<b>Thickness (imperial)</b>	0.04 "
<b>Thickness (metric)</b>	1.1 mm
<b>Width (imperial)</b>	0.14 "
<b>Width (metric)</b>	3.6 mm

LFH ✓

RoHS ✓