

TECHNICAL DATA SHEET

Part No. 111-02447
Article No. 111-02447
Type T50R



The PVDF cable tie is rated for 25 years' performance outdoors. It provides some of the highest UV, chemical and thermal resistance of any plastic resin. It functions just like our standard ties, simple and fast, streamlining installation and providing reliable performance.

Material	Polyvinylidene Fluoride (PVDF)
Operating Temperature	-40°F to +284°F (-40°C to +140°C)
Flammability	UL 94 V-0
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Gray (GY)
Pkg. Qty.	3000
Carton Qty.	3000
Customs Number	3926909988

Cable Tie Head Length (imperial)	0.29 "
Cable Tie Head Length (metric)	7.3 mm
Cable Tie Head Width (imperial)	0.3 "
Cable Tie Head Width (metric)	7.6 mm
Length (imperial)	7.95 "
Length (metric)	202.0 mm
Max. Bundle Diameter (imperial)	1.97 "
Max. Bundle Diameter (metric)	50.0 mm
Min. Tensile Strength (imperial)	50 lbs
Min. Tensile Strength (metric)	225 N
Serration Side	Inside Serrated
Thickness (imperial)	0.47 "
Thickness (metric)	1.2 mm
Width (imperial)	0.19 "
Width (metric)	4.7 mm

