

TECHNICAL DATA SHEET

Part No. T30R3M4
Article No. 111-03052
Type T30R



T-Series Cable Ties feature inside serrations to provide a positive hold on wire and cable bundles. The head design guarantees high tensile strength and a low insertion force. The bent tail design allows quick and simple installations by hand. For high-volume applications, tensioning tools are available to ensure consistent and safe installation. Specially manufactured to comply with Military Specification MS3367-5-3, Class 1 and SAE-AS33671.

Material	Polyamide 6.6 (PA66)
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Flammability	UL 94 V-2
Halogen Free	Yes
Plenum Rating	AH-2
UV Resistant	No
US MILSPEC	MS3367-5-3, Class 1, SAE-AS33671
Use Conditions	For Indoor Use Only
Color	Orange (OG)

Pkg. Qty.	1000
Carton Qty.	5000
Customs Number	3926909988

Length (imperial)	5.83 "
Length (metric)	148.0 mm
Max. Bundle Diameter (imperial)	1.38 "
Max. Bundle Diameter (metric)	35.0 mm
Min. Tensile Strength (imperial)	30 lbs
Min. Tensile Strength (metric)	135 N
Serration Side	Inside Serrated
Thickness (metric)	1.1 mm
Width (imperial)	0.14 "
Width (metric)	3.6 mm

