

TECHNICAL DATA SHEET

Part No. 111-05350
Article No. 111-05350
Type T50IFT7



HellermannTyton's fir tree mounts provide a secure grip in a mounting hole. The mount can slide along the cable tie to adjust orientation as needed. Fir tree mounts are designed to provide a low insertion force and high extraction force. This mount is sold as an assembly with the cable tie.

Material	Polyamide 6.6 heat stabilized (PA66HS)
Material Cable Tie	PA66HS
Material Foot Part	PA66HS
Operating Temperature	-40°F to +257°F (-40°C to +125°C)
Foot Part Operating Temperature	-40°F to +257°F (-40°C to +125°C)
Flammability	UL 94 V-2
UV Resistant	No
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	500
Carton Qty.	2000
Customs Number	3926909988

Cable Tie Head Length (imperial)	0.27 "
Cable Tie Head Length (metric)	7.0 mm
Cable Tie Head Width (imperial)	0.31 "
Cable Tie Head Width (metric)	7.8 mm
Fixation Method	Fir tree for round holes
Height (imperial)	0.0472 "
Height (metric)	1.2 mm
Length (imperial)	11.8 "
Length (metric)	305.0 mm
Length 2 (imperial)	0.46 "
Length 2 (metric)	11.6 mm
Max. Bundle Diameter (imperial)	3.35 "
Max. Bundle Diameter (metric)	85.0 mm
Min. Tensile Strength (imperial)	50 lbs
Min. Tensile Strength (metric)	225 N
Mounting Hole Diameter (imperial)	0.26 - 0.28 "
Mounting Hole Diameter (metric)	6.5 - 7.0 mm
Panel Thickness (imperial)	0.03 - 0.28 "
Panel Thickness (metric)	0.8 - 7.0 mm
Thickness (metric)	1.2 mm
Width (imperial)	0.18 "
Width (metric)	4.6 mm

RoHS ✓