

TECHNICAL DATA SHEET

Part No. T120L0K2
Article No. 111-12405
Type T120L



Heavy duty T-Series cable ties feature inside serrations to provide a positive hold on wire and cable bundles. Durable head design guarantees high tensile strength and a low insertion force. For high-volume applications, tensioning tools are available to ensure consistent and safe installation.

Material	Polyamide 6.6 (PA66)
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Flammability	UL 94 V-2
Halogen Free	Yes
Plenum Rating	AH-2
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	50
Carton Qty.	1000
Customs Number	3926909988

Cable Tie Head Length (imperial)	0.39 "
Cable Tie Head Length (metric)	10.0 mm
Cable Tie Head Width (imperial)	0.51 "
Cable Tie Head Width (metric)	13.0 mm
Height (metric)	7.8 mm
Length (imperial)	30.0 "
Length (metric)	760.0 mm
Max. Bundle Diameter (imperial)	8.86 "
Max. Bundle Diameter (metric)	225.0 mm
Min. Tensile Strength (imperial)	120 lbs
Min. Tensile Strength (metric)	535 N
Serration Side	Inside Serrated
Thickness (imperial)	0.075 "
Thickness (metric)	1.9 mm
Width (imperial)	0.30 "
Width (metric)	7.6 mm

