

TECHNICAL DATA SHEET

Part No. T120S0PPH4
Article No. 111-12827
Type T120S



HellermannTyton's polypropylene cable ties offer added resistance to most chemicals. T-Series cable ties feature inside serrations to provide a positive hold on wire and cable bundles. The head design guarantees high tensile strength and a low insertion force. For high-volume applications, tensioning tools are available to ensure consistent and safe installation.

Material	Polypropylene (PP)
Operating Temperature	-40°F to +239°F (-40°C to +115°C)
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant	No
Use Conditions	For Indoor Use Only
Color	Black (BK)
Pkg. Qty.	500
Carton Qty.	1000
Customs Number	3926909988

Cable Tie Head Length (imperial)	0.39 "
Cable Tie Head Length (metric)	10.0 mm
Cable Tie Head Width (imperial)	0.52 "
Cable Tie Head Width (metric)	13.15 mm
Height (metric)	7.7 mm
Length (imperial)	8.86 "
Length (metric)	225.0 mm
Max. Bundle Diameter (imperial)	2.17 "
Max. Bundle Diameter (metric)	55.0 mm
Min. Tensile Strength (imperial)	60 lbs
Min. Tensile Strength (metric)	267 N
Serration Side	Inside Serrated
Thickness (imperial)	0.06 "
Thickness (metric)	1.6 mm
Width (imperial)	0.30 "
Width (metric)	7.6 mm

