

TECHNICAL DATA SHEET

Part No. IT18R6L4
Article No. 111-81805
Type IT18R



Identification Cable Ties feature an identification plate that allows wire and cable bundles to be easily marked and identified. These ties enable wire and cables to be secured and identified using just one product, saving installation time. The plates can be marked using a permanent marker or with a HellermannTyton adhesive label. Specially manufactured to comply with Military Specification MS3368-5-6E, Class 1 and SAE-AS33681.

Material	Polyamide 6.6 (PA66)
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Flammability	UL 94 V-2
Halogen Free	Yes
UV Resistant	No
Use Conditions	For Indoor Use Only
Color	Blue (BU)
Pkg. Qty.	200
Carton Qty.	10000
Customs Number	3926909988

Height (imperial)	0.32 "
Height (metric)	8.0 mm
Length (imperial)	3.9 "
Length (metric)	100.0 mm
Max. Bundle Diameter (imperial)	0.75 "
Max. Bundle Diameter (metric)	19.0 mm
Min. Tensile Strength (metric)	80 N
Width (imperial)	0.98 "
Width (metric)	25.0 mm
Width 2 (imperial)	0.09 "
Width 2 (metric)	2.4 mm

