

TECHNICAL DATA SHEET

Part No. IT18FL3L4
Article No. 111-81909
Type IT18FL



Identification cable ties feature an identification plate that allows wire and cable bundles to be easily marked and identified. These ties enable wire and cables to be secured and identified using just one product, saving installation time. The plates can be marked using a permanent marker or with a HellermannTyton adhesive label.

Material	Polyamide 6.6 (PA66)
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Flammability	UL 94 V-2
Halogen Free	Yes
UV Resistant	No
Use Conditions	For Indoor Use Only
Color	Orange (OG)
Pkg. Qty.	200
Carton Qty.	10000
Customs Number	3926909988

Height (imperial)	0.35 "
Height (metric)	9.0 mm
Length (imperial)	4.3 "
Length (metric)	110.0 mm
Max. Bundle Diameter (imperial)	0.75 "
Max. Bundle Diameter (metric)	19.0 mm
Min. Tensile Strength (metric)	80 N
Width (imperial)	0.81 "
Width (metric)	20.5 mm
Width 2 (imperial)	0.1 "
Width 2 (metric)	2.5 mm

