

TECHNICAL DATA SHEET

Part No. T30RSF9C2
Article No. 111-85603
Type T30RSF(U)



One-piece mounting ties offer a complete solution by both bundling cable and simultaneously providing a mounting solution. The arrowhead design of this push mount inserts easily and locks securely in place. HellermannTyton's one-piece mounting ties combine high-specification materials with superior design to deliver dependable performance in a range of applications.

Material	Polyamide 6.6 (PA66)
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Flammability	UL 94 V-2
UV Resistant	No
Use Conditions	For Indoor Use Only
Color	Natural (NA)
Pkg. Qty.	100
Carton Qty.	5000
Customs Number	3926909988

Fixation Method	Arrowhead
Height (imperial)	.20 "
Height (metric)	5.80 mm
Length (imperial)	6.3 "
Length (metric)	160.02 mm
Max. Bundle Diameter (imperial)	1.26 "
Max. Bundle Diameter (metric)	32.0 mm
Min. Tensile Strength (imperial)	30 lbs
Min. Tensile Strength (metric)	136 N
Mounting Hole Diameter (imperial)	0.19 - 0.22 "
Mounting Hole Diameter (metric)	4.7 - 5.6 mm
Panel Thickness (imperial)	0.03 - 0.09 "
Panel Thickness (metric)	0.75 - 2.1 mm
Thickness (imperial)	0.05 "
Thickness (metric)	1.2 mm
Width (imperial)	0.14 "
Width (metric)	3.6 mm

RoHS✓

