

TECHNICAL DATA SHEET

Part No. MBT8H-S
Article No. 111-94088
Type MBT8HS



HellermannTyton's Stainless Steel Ties are designed with a ball bearing locking mechanism to ensure high tensile strength and easy insertion when securing hoses, cables, pipes and more. Stainless steel provides protection when used in corrosive environments, fire resistance and temperature extremes.

Material	Stainless Steel (SS304)
Operating Temperature	-112°F to +1000°F (-80°C to +538°C)
Flammability	Non-burning
Halogen Free	Yes
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Metal (ML)

Pkg. Qty.	50
Carton Qty.	2000
Customs Number	7326908695

Length (imperial)	7.9 "
Length (metric)	201.0 mm
Max. Bundle Diameter (imperial)	1.97 "
Max. Bundle Diameter (metric)	50.0 mm
Min. Tensile Strength (imperial)	450 lbs
Min. Tensile Strength (metric)	2000 N
Thickness (imperial)	0.01 "
Thickness (metric)	0.3 mm
Width (imperial)	0.31 "
Width (metric)	7.9 mm

HF ✓

LFH ✓

RoHS ✓

