

TECHNICAL DATA SHEET

Part No. MBT14H
Article No. 111-94149
Type MBT14H



HellermannTyton's Stainless Steel Ties are designed with a ball bearing locking mechanism to ensure high tensile strength and easy insertion when securing hoses, cables, pipes and more. Stainless steel ties can be used in virtually any indoor, outdoor or underground application. Grade 316 material is highly resistant to corrosion and widely used in marine environments where chemicals, salts, acids and temperature extremes may affect the bundling application.

Material	Stainless Steel (SS316L)
Operating Temperature	-112°F to +1000°F (-80°C to +538°C)
Flammability	Non-burning
Halogen Free	Yes
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Metal (ML)
Pkg. Qty.	50
Carton Qty.	2000
Customs Number	7326908695

Length (imperial)	14.3 "
Length (metric)	362.0 mm
Max. Bundle Diameter (imperial)	4.02 "
Max. Bundle Diameter (metric)	102.0 mm
Min. Tensile Strength (imperial)	450 lbs
Min. Tensile Strength (metric)	2000 N
Thickness (imperial)	0.01 "
Thickness (metric)	0.3 mm
Width (imperial)	0.31 "
Width (metric)	7.9 mm

HF ✓ LFH ✓

RoHS ✓

