

TECHNICAL DATA SHEET

Part No. 112-00062
Article No. 112-00062
Type LPT50R



HellermannTyton Low Profile Cable Ties feature a compact, contoured head designed to use less space in confined areas and reduce protrusions that might otherwise interfere with or damage adjacent wire insulation and hoses. The outside serration provides a smooth inside surface to further minimize indentation or damage to soft bundles. The low profile cable tie delivers high tensile strength with low insertion force.

Material	Polyamide 6.6 heat stabilized (PA66HS)
Operating Temperature	-40°F to +257°F (-40°C to +125°C)
Flammability	UL 94 V-2
Halogen Free	Yes
UV Resistant	No
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	100
Carton Qty.	5000
Customs Number	3926909988

Length (imperial)	7.7 "
Length (metric)	194.6 mm
Max. Bundle Diameter (metric)	51.0 mm
Min. Tensile Strength (imperial)	50 lbs
Min. Tensile Strength (metric)	223 N
Width (imperial)	0.2 "
Width (metric)	4.8 mm

