

TECHNICAL DATA SHEET

Part No. T40R0C2
Article No. 112-04060
Type T40R(U)



T-Series Cable Ties feature inside serrations to provide a positive hold on wire and cable bundles. The head design guarantees high tensile strength and a low insertion force. The bent tail design allows quick and simple installations by hand. For high-volume applications, tensioning tools are available to ensure consistent and safe installation.

Material	Polyamide 6.6 (PA66)
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Flammability	UL 94 V-2
Halogen Free	Yes
Plenum Rating	AH-2
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	100
Carton Qty.	5000
Customs Number	3926909988

Length (imperial)	8.30 "
Length (metric)	210.82 mm
Max. Bundle Diameter (imperial)	2.17 "
Max. Bundle Diameter (metric)	55.0 mm
Min. Tensile Strength (imperial)	40 lbs
Min. Tensile Strength (metric)	180 N
Serration Side	Inside Serrated
Width (imperial)	0.16 "
Width (metric)	4.0 mm

