

TECHNICAL DATA SHEET

Part No. T50I9C2
Article No. 112-05219
Type T50I



T-Series Cable Ties feature inside serrations to provide a positive hold on wire and cable bundles. The head design guarantees high tensile strength and a low insertion force. The bent tail design allows quick and simple installations by hand. For high-volume applications, tensioning tools are available to ensure consistent and safe installation.

Material	Polyamide 6.6 (PA66)
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Flammability	UL 94 V-2
Halogen Free	Yes
Plenum Rating	AH-2
UV Resistant	No
Use Conditions	For Indoor Use Only
Color	Natural (NA)
Pkg. Qty.	100
Carton Qty.	5000
Customs Number	3926909988

Cable Tie Head Length (imperial)	0.27 "
Cable Tie Head Length (metric)	7.0 mm
Cable Tie Head Width (imperial)	0.31 "
Cable Tie Head Width (metric)	7.8 mm
Length (imperial)	12.0 "
Length (metric)	305.0 mm
Max. Bundle Diameter (imperial)	3.15 "
Max. Bundle Diameter (metric)	80.0 mm
Min. Tensile Strength (imperial)	50 lbs
Min. Tensile Strength (metric)	225 N
Serration Side	Inside Serrated
Thickness (imperial)	0.05 "
Thickness (metric)	1.2 mm
Width (imperial)	0.18 "
Width (metric)	4.6 mm

