

TECHNICAL DATA SHEET

Part No. CTT20R0C2
Article No. 112-51900
Type CTT20R



HellermannTyton clamp tie has triangular shaped tabs extending beneath the head for optimal surface contact and complete circumferential compression to 360 degrees. The bent tail design allows quick and simple installations by hand. The clamps are recommended for soft rubber hose applications including fuel, water, and air vacuum lines.

Material	Polyamide 6.6 (PA66)
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Flammability	UL 94 V-2
UV Resistant	No
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	100
Carton Qty.	10000
Customs Number	3926909988

Length (imperial)	4.0 "
Length (metric)	101.6 mm
Max. Bundle Diameter (imperial)	0.51 "
Max. Bundle Diameter (metric)	13.0 mm
Min. Tensile Strength (imperial)	20 lbs
Min. Tensile Strength (metric)	90 N
Serration Side	Inside Serrated
Width (imperial)	0.10 "
Width (metric)	2.5 mm

