

TECHNICAL DATA SHEET

Part No. CTT20R0HSC2
Article No. 112-51905
Type CTT20R



The 360 degree compression ties are designed with underside clamping rails to allow for optimal surface contact and complete circumferential compression around the bundle. The bent tail design allows quick and simple installations by hand. For high-volume applications, tensioning tools are available to ensure consistent and safe installation.

Material	Polyamide 6.6 heat stabilized (PA66HS)
Operating Temperature	-40°F to +257°F (-40°C to +125°C)
Flammability	UL 94 V-2
UV Resistant	No
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	100
Carton Qty.	10000
Customs Number	3926909988

Length (imperial)	4.0 "
Length (metric)	101.6 mm
Max. Bundle Diameter (imperial)	0.51 "
Max. Bundle Diameter (metric)	13.0 mm
Min. Tensile Strength (imperial)	20 lbs
Min. Tensile Strength (metric)	90 N
Serration Side	Inside Serrated
Thickness (imperial)	0.043 "
Thickness (metric)	1.1 mm
Width (imperial)	0.10 "
Width (metric)	2.5 mm

