

TECHNICAL DATA SHEET

Part No. T18MR9M4
Article No. 113-00028
Type T18MR



1-piece Screw Mount Cable Ties fasten with a screw or bolt to provide secure routing of cable bundles. Multiple configurations are available to cover a range of bundle sizes and tensile strengths.

Material	Polyamide 6.6 (PA66)
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Flammability	UL 94 V-2
Plenum Rating	AH-2
UV Resistant	No
Use Conditions	For Indoor Use Only
Color	Natural (NA)
Pkg. Qty.	1000
Carton Qty.	10000
Customs Number	3926909988

Fixation Method	Screw Mount
Height (imperial)	.17 "
Height (metric)	4.20 mm
Length (imperial)	4.3 "
Length (metric)	110.0 mm
Max. Bundle Diameter (imperial)	0.79 "
Max. Bundle Diameter (metric)	20.0 mm
Min. Tensile Strength (imperial)	18 lbs
Min. Tensile Strength (metric)	80 N
Mounting Screw Type	#4 (M2.5) Screw
Thickness (imperial)	0.039 "
Thickness (metric)	1.0 mm
Width (imperial)	0.1 "
Width (metric)	2.5 mm

