

TECHNICAL DATA SHEET

Part No. T50MI0M4
Article No. 113-00031
Type T50MI



One-piece Screw Mount Cable Ties fasten with a screw or bolt to provide secure routing of cable bundles. Multiple configurations are available to cover a range of bundle sizes and tensile strengths.

Material	Polyamide 6.6 (PA66)
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Flammability	UL 94 V-2
Plenum Rating	AH-2
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	1000
Carton Qty.	5000
Customs Number	3926909988

Fixation Method	Screw Mount
Height (imperial)	.23 "
Height (metric)	5.70 mm
Length (imperial)	12.4 "
Length (metric)	315.0 mm
Max. Bundle Diameter (imperial)	3.35 "
Max. Bundle Diameter (metric)	85.0 mm
Min. Tensile Strength (imperial)	50 lbs
Min. Tensile Strength (metric)	225 N
Mounting Screw Type	#10 Screw
Width (imperial)	0.19 "
Width (metric)	4.7 mm

RoHS ✓

