

TECHNICAL DATA SHEET

Part No. 113-00060
Article No. 113-00060
Type T50MRX



Screw Mount Cable Ties attach to existing holes using a screw or bolt to provide a fastening point to secure and route wire and cable bundles. Reinforced ribs between the screw mount and cable tie head provide additional strength for added bundle stability and security.

Material	Polyamide 6.6 heat stabilized (PA66HS)
Operating Temperature	-40°F to +257°F (-40°C to +125°C)
Flammability	UL 94 V-2
Plenum Rating	AH-2
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	100
Carton Qty.	5000
Customs Number	3926909988

Fixation Method	Screw Mount
Height (imperial)	.24 "
Height (metric)	6.0 mm
Length (imperial)	8.0 "
Length (metric)	203.2 mm
Max. Bundle Diameter (imperial)	1.77 "
Max. Bundle Diameter (metric)	45.0 mm
Min. Tensile Strength (imperial)	50 lbs
Min. Tensile Strength (metric)	225 N
Mounting Screw Type	1/4" (M6) Screw
Width (imperial)	0.2 "
Width (metric)	4.7 mm

RoHS ✓

