

TECHNICAL DATA SHEET

Part No. T120MR0HSH4
Article No. 113-00073
Type T120MR



One-piece screw mount cable ties fasten with a screw or bolt to provide secure routing of cable bundles. Multiple configurations are available to cover a range of bundle sizes and tensile strengths.

Material	Polyamide 6.6 heat stabilized (PA66HS)
Operating Temperature	-40°F to +257°F (-40°C to +125°C)
Flammability	UL 94 V-2
Plenum Rating	AH-2
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	500
Carton Qty.	1000
Customs Number	3926909988

Cable Tie Head Length (imperial)	1.1 "
Cable Tie Head Length (metric)	28.4 mm
Cable Tie Head Width (imperial)	0.5 "
Cable Tie Head Width (metric)	13.4 mm
Fixation Method	Screw Mount
Height (imperial)	0.31 "
Height (metric)	7.9 mm
Length (imperial)	15.6 "
Length (metric)	395.0 mm
Max. Bundle Diameter (imperial)	4.02 "
Max. Bundle Diameter (metric)	102.0 mm
Min. Tensile Strength (imperial)	120 lbs
Min. Tensile Strength (metric)	535 N
Mounting Screw Type	1/4" (M6) Screw
Thickness (imperial)	0.07 "
Thickness (metric)	1.8 mm
Width (imperial)	0.30 "
Width (metric)	7.6 mm

