

TECHNICAL DATA SHEET

Part No. T50MR0HSM4
Article No. 113-05013
Type T50MR



One-piece Screw Mount Cable Ties fasten with a screw or bolt to provide secure routing of cable bundles. Multiple configurations are available to cover a range of bundle sizes and tensile strengths.

Material	Polyamide 6.6 heat stabilized (PA66HS)
Operating Temperature	-40°F to +257°F (-40°C to +125°C)
Flammability	UL 94 V-2
Plenum Rating	AH-2
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	1000
Carton Qty.	5000
Customs Number	3926909988

Cable Tie Head Length (imperial)	1.1 "
Cable Tie Head Length (metric)	28.4 mm
Cable Tie Head Width (imperial)	0.5 "
Cable Tie Head Width (metric)	13.4 mm
Fixation Method	Screw Mount
Height (imperial)	0.22 "
Height (metric)	5.5 mm
Length (imperial)	8.5 "
Length (metric)	215.9 mm
Max. Bundle Diameter (imperial)	1.77 "
Max. Bundle Diameter (metric)	45.0 mm
Min. Tensile Strength (imperial)	50 lbs
Min. Tensile Strength (metric)	225 N
Mounting Screw Type	#10 (M5) Screw
Thickness (imperial)	0.05 "
Thickness (metric)	1.2 mm
Width (imperial)	0.18 "
Width (metric)	4.7 mm

RoHS ✓

