

TECHNICAL DATA SHEET

Part No. T50ML9C2
Article No. 113-05419
Type T50ML



1-piece Screw Mount Cable Ties fasten with a screw or bolt to provide secure routing of cable bundles. Multiple configurations are available to cover a range of bundle sizes and tensile strengths.

Material	Polyamide 6.6 (PA66)
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Flammability	UL 94 V-2
Plenum Rating	AH-2
UV Resistant	No
Use Conditions	For Indoor Use Only
Color	Natural (NA)
Pkg. Qty.	100
Carton Qty.	5000
Customs Number	3926909988

Cable Tie Head Length (imperial)	1.1 "
Cable Tie Head Length (metric)	28.4 mm
Cable Tie Head Width (imperial)	0.5 "
Cable Tie Head Width (metric)	13.4 mm
Fixation Method	Screw Mount
Height (imperial)	0.23 "
Height (metric)	5.7 mm
Length (imperial)	15.4 "
Length (metric)	390.0 mm
Max. Bundle Diameter (imperial)	3.94 "
Max. Bundle Diameter (metric)	100.0 mm
Min. Tensile Strength (imperial)	50 lbs
Min. Tensile Strength (metric)	225 N
Mounting Screw Type	#10 (M5) Screw
Thickness (imperial)	0.05 "
Thickness (metric)	1.2 mm
Width (imperial)	0.18 "
Width (metric)	4.7 mm

RoHS 

