

TECHNICAL DATA SHEET

Part No. RTT750HR.NX900
Article No. 115-00001
Type SpeedyTie (RTT750HR)



HellermannTyton releasable cable ties offer a release feature in the head allowing for easy access to wire bundles when changes or temporary bundling are necessary. The head design guarantees high tensile strength even after repeated use.

Material	Polyamide 6.6 (PA66)
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Flammability	UL 94 V-2
UV Resistant	No
Use Conditions	For Indoor Use Only
Color	Yellow (YE), Red (RD)
Pkg. Qty.	5
Carton Qty.	60
Customs Number	3926909988

Length (imperial)	29.6 "
Length (metric)	752.0 mm
Max. Bundle Diameter (metric)	210.0 mm
Min. Tensile Strength (imperial)	200 lbs
Min. Tensile Strength (metric)	888 N
Thickness (imperial)	0.075 "
Thickness (metric)	1.9 mm
Width (imperial)	0.51 "
Width (metric)	13.0 mm

RoHS 