

TECHNICAL DATA SHEET

Part No. RT40R9M4
Article No. 115-06204
Type RT40R



HellermannTyton releasable cable ties offer a release feature in the head allowing for easy access to wire bundles when changes are necessary. The head design guarantees high tensile strength even after repeated use, as well as a low insertion force. For high volume applications, tensioning tools are available to ensure consistent and safe installation.

Material	Polyamide 6.6 (PA66)
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Flammability	UL 94 V-2
UV Resistant	No
Use Conditions	For Indoor Use Only
Color	Natural (NA)
Pkg. Qty.	1000
Carton Qty.	5000
Customs Number	3926909988

Length (imperial)	8.5 "
Length (metric)	215.9 mm
Max. Bundle Diameter (metric)	51.0 mm
Min. Tensile Strength (imperial)	40 lbs
Min. Tensile Strength (metric)	180 N
Width (imperial)	0.16 "
Width (metric)	4.0 mm

RoHS 

