

TECHNICAL DATA SHEET

Part No. 115-06960
Article No. 115-06960
Type RT50SFK



One-piece mounting ties offer a complete solution by bundling cables while at the same time providing a mounting solution. This tie features an extended pawl, allowing the user to release the tie for bundle maintenance. Push mount ties offer the ideal combination of high specification materials and superior design to suit the mounting and bundling needs of complex applications.

Material	Polyamide 6.6 (PA66)
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Flammability	UL 94 V-2
UV Resistant	No
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	1000
Carton Qty.	6000
Customs Number	3926909988

Fixation Method	Arrowhead
Height (imperial)	0.24 "
Height (metric)	6 mm
Length (imperial)	9.0 "
Length (metric)	225 mm
Max. Bundle Diameter (imperial)	1.97 "
Max. Bundle Diameter (metric)	50.0 mm
Min. Tensile Strength (imperial)	50 lbs
Min. Tensile Strength (metric)	225 N
Mounting Hole Diameter (imperial)	0.25 - 0.28 "
Mounting Hole Diameter (metric)	6.4 - 7.0 mm
Panel Thickness (imperial)	0.03 - 0.11 "
Panel Thickness (metric)	0.8 - 3.0 mm
Thickness (imperial)	0.055 "
Thickness (metric)	1.4 mm
Width (imperial)	0.2 "
Width (metric)	5.0 mm

