

# TECHNICAL DATA SHEET

**Part No.** 115-07190  
**Article No.** 115-07190  
**Type** SOFTFIX XS



Soft, flexible material makes these ties particularly suitable for use on sensitive wires, such as fiber-optic cables. Additionally the ties are suitable for use on moving or vibrating applications. The double slotted head allows for parallel bundling.

|                              |                                  |
|------------------------------|----------------------------------|
| <b>Material</b>              | Thermoplastic Polyurethane (TPU) |
| <b>Operating Temperature</b> | -40°F to +185°F (-40°C to +85°C) |
| <b>Flammability</b>          | UL 94 HB                         |
| <b>Halogen Free</b>          | Yes                              |
| <b>UV Resistant</b>          | No                               |
| <b>Use Conditions</b>        | For Indoor Use Only              |
| <b>Color</b>                 | Black (BK)                       |
| <b>Pkg. Qty.</b>             | 16                               |
| <b>Carton Qty.</b>           | 19                               |
| <b>Customs Number</b>        | 3926909988                       |

|                                       |         |
|---------------------------------------|---------|
| <b>Length (imperial)</b>              | 7.0 "   |
| <b>Length (metric)</b>                | 180 mm  |
| <b>Max. Bundle Diameter (metric)</b>  | 45.0 mm |
| <b>Min. Tensile Strength (metric)</b> | 57 N    |
| <b>Thickness (metric)</b>             | 1.7 mm  |
| <b>Width (metric)</b>                 | 7.0 mm  |

