

TECHNICAL DATA SHEET

Part No. 115-11349
Article No. 115-11349
Type SRT34011



Soft, flexible material makes these ties particularly suitable for use on sensitive wires, such as fibre-optic cables. Additionally the ties are suitable for use on moving or vibrating applications. The double slotted head allows for parallel bundling.

Material	Thermoplastic Polyurethane (TPU)
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant	No
Use Conditions	For Indoor Use Only
Color	Black (BK)
Pkg. Qty.	50
Carton Qty.	750
Customs Number	3926909988

Length (imperial)	13.39 "
Length (metric)	340 mm
Max. Bundle Diameter (metric)	90.0 mm
Min. Tensile Strength (metric)	123 N
Thickness (metric)	2.3 mm
Width (metric)	11.0 mm

