

TECHNICAL DATA SHEET

Part No. 115-28589
Article No. 115-28589
Type SRT58028



Soft, flexible material makes these ties particularly suitable for use on sensitive wires, such as fiber-optic cables. Additionally the ties are suitable for use on moving or vibrating applications. The double slotted head allows for parallel bundling.

Material	Thermoplastic Polyurethane (TPU)
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant	No
Use Conditions	For Indoor Use Only
Color	Black (BK)
Pkg. Qty.	10
Carton Qty.	200
Customs Number	3926909988

Length (imperial)	22.83 "
Length (metric)	580 mm
Max. Bundle Diameter (metric)	150 mm
Min. Tensile Strength (metric)	360 N
Thickness (metric)	3.4 mm
Width (metric)	28.0 mm

