

TECHNICAL DATA SHEET

Part No. DCT110HIRK2
Article No. 115-31100
Type DCT11



Dual-Clamp Ties are designed to provide parallel separation between hoses, wires, cables, and tubing to protect them from abrasion. These ties have an optional mounting hole for securing bundles along the chassis of trucks, trailers, and heavy duty equipment. The unique one-piece design features the dual head centered on the strap.

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Operating Temperature, 500h	+329°F (+165°C)
Operating Temperature, 1000h	+320°F (+160°C)
Operating Temperature, 5000h	+257°F (+125°C)
Flammability	UL 94 HB
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)

Pkg. Qty.	50
Carton Qty.	500
Customs Number	3926909988

Fixation Method	Weld Stud Fixing
Height (imperial)	0.8 "
Height (metric)	20.32 mm
Length (imperial)	19.2 "
Length (metric)	487.68 mm
Max. Bundle Diameter (imperial)	2.28 "
Max. Bundle Diameter (metric)	58.0 mm
Min. Tensile Strength (imperial)	150 lbs
Min. Tensile Strength (metric)	667 N
Stud Diameter (imperial)	1/4 "
Stud Diameter (metric)	M6
Thickness (imperial)	0.06 "
Thickness (metric)	1.4 mm
Width (imperial)	0.5 "
Width (metric)	12.7 mm

RoHS ✓