

TECHNICAL DATA SHEET

Part No. SR255S0HIHSUVX2
Article No. 115-42002
Type SR255S



HellermannTyton SR255 Series heavy-duty cable ties offer a release feature in the head allowing for easy installation with the use of a cable tie tool. The head design guarantees high tensile strength even after repeated use, as well as a low insertion force.

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Flammability	UL 94 HB
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	25
Carton Qty.	1000
Customs Number	3926909988

Length (imperial)	8.9 "
Length (metric)	225.0 mm
Max. Bundle Diameter (metric)	50.0 mm
Min. Tensile Strength (imperial)	250 lbs
Min. Tensile Strength (metric)	1115 N
Width (imperial)	0.5 "
Width (metric)	12.6 mm

