

TECHNICAL DATA SHEET

Part No. 117-00012
Article No. 117-00012
Type SDCTR312



Stand Off Dual Clamp Ties offer the same features as the standard dual clamp tie, with a standoff mount that secures the bundle away from the side of the frame rail. This protects the bundles from bolts and other protrusions.

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Flammability	UL 94 HB
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	250
Carton Qty.	250
Customs Number	3926909988

Fixation Method	Weld Stud Fixing
Height (imperial)	1.47 "
Height (metric)	37.30 mm
Length (imperial)	20.1 "
Length (metric)	510.5 mm
Max. Bundle Diameter (imperial)	2.3 "
Max. Bundle Diameter (metric)	58.4 mm
Min. Tensile Strength (imperial)	100 lbs
Min. Tensile Strength (metric)	445 N
Stud Diameter (imperial)	5/16 "
Stud Diameter (metric)	M8
Width (imperial)	0.5 "
Width (metric)	12.7 mm

RoHS

