

TECHNICAL DATA SHEET

Part No. T50IDH0M4
Article No. 117-05300
Type T50IDH



The double head cable tie was designed with a dual locking head that creates two loops to secure two bundles simultaneously. The head also provides separation between bundles or bundles running parallel to each other. The bent tail design allows quick and simple installations by hand. For high volume applications, tensioning tools are available to ensure consistent and safe installation.

Material	Polyamide 6.6 (PA66)
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Flammability	UL 94 V-2
Halogen Free	Yes
UV Resistant	No
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	1000
Carton Qty.	5000
Customs Number	3926909988

Cable Tie Head Length (imperial)	0.27 "
Cable Tie Head Length (metric)	7.0 mm
Cable Tie Head Width (imperial)	0.31 "
Cable Tie Head Width (metric)	7.8 mm
Length (imperial)	12.0 "
Length (metric)	305.0 mm
Max. Bundle Diameter (imperial)	3 "
Max. Bundle Diameter (metric)	76.2 mm
Min. Tensile Strength (imperial)	50 lbs
Min. Tensile Strength (metric)	225 N
Serration Side	Inside Serrated
Thickness (metric)	1.4 mm
Width (imperial)	0.19 "
Width (metric)	4.7 mm

