

TECHNICAL DATA SHEET

Part No. T50LDH0HSM4
Article No. 117-05404
Type T50LDH



The double head cable tie was designed with a dual locking head that creates two loops to secure two bundles simultaneously. The head also provides separation between bundles or bundles running parallel to each other. The bent tail design allows quick and simple installations by hand. For high volume applications, tensioning tools are available to ensure consistent and safe installation.

Material	Polyamide 6.6 heat stabilized (PA66HS)
Operating Temperature	-40°F to +257°F (-40°C to +125°C)
Flammability	UL 94 V-2
Halogen Free	Yes
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	1000
Carton Qty.	5000
Customs Number	3926909988

Length (imperial)	15.60 "
Length (metric)	395.0 mm
Max. Bundle Diameter (imperial)	4 "
Max. Bundle Diameter (metric)	101.6 mm
Min. Tensile Strength (imperial)	50 lbs
Min. Tensile Strength (metric)	225 N
Serration Side	Inside Serrated
Thickness (metric)	1.4 mm
Width (imperial)	0.19 "
Width (metric)	4.7 mm

