

TECHNICAL DATA SHEET

Part No. T120RDH0K2
Article No. 117-05501
Type T120RDH



The double head cable tie was designed with a dual locking head that creates two loops to secure two bundles simultaneously. The head also provides separation between bundles or bundles running parallel to each other. For high volume applications, tensioning tools are available to ensure consistent and safe installation.

Material	Polyamide 6.6 (PA66)
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Flammability	UL 94 V-2
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	50
Carton Qty.	1000
Customs Number	3926909988

Cable Tie Head Length (imperial)	0.9 "
Cable Tie Head Length (metric)	22.9 mm
Cable Tie Head Width (imperial)	0.48 "
Cable Tie Head Width (metric)	12.3 mm
Length (imperial)	15.7 "
Length (metric)	398.0 mm
Max. Bundle Diameter (imperial)	4.0 "
Max. Bundle Diameter (metric)	101.6 mm
Min. Tensile Strength (imperial)	120 lbs
Min. Tensile Strength (metric)	534 N
Serration Side	Inside Serrated
Thickness (imperial)	0.07 "
Thickness (metric)	1.8 mm
Width (imperial)	0.30 "
Width (metric)	7.6 mm

RoHS✓

