

TECHNICAL DATA SHEET

Part No. 118-05900
Article No. 118-05900
Type T50LOS



HellermannTyton outside serrated cable ties are designed with a smooth inside surface to help minimize indentation or damage to wire and cable insulation, while offering high tensile strength and low insertion force. The contour style head takes up less space than traditional style cable ties making it ideal for space constrained areas. For high volume applications, tensioning tools are available to ensure consistent and safe installation.

Material	Polyamide 6.6 heat stabilized (PA66HS)
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Flammability	UL 94 V-2
Halogen Free	Yes
UV Resistant	No
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	100
Carton Qty.	4000
Customs Number	3926909988

Cable Tie Head Length (imperial)	0.26 "
Cable Tie Head Length (metric)	6.75 mm
Cable Tie Head Width (imperial)	0.31 "
Cable Tie Head Width (metric)	7.9 mm
Height (imperial)	0.05 "
Height (metric)	1.3 mm
Length (imperial)	15.2 "
Length (metric)	384.0 mm
Max. Bundle Diameter (imperial)	4.33 "
Max. Bundle Diameter (metric)	110.0 mm
Min. Tensile Strength (imperial)	50 lbs
Min. Tensile Strength (metric)	225 N
Serration Side	Outside Serrated
Thickness (imperial)	0.05 "
Thickness (metric)	1.3 mm
Width (imperial)	0.18 "
Width (metric)	4.6 mm

HF ✓

RoHS ✓