

TECHNICAL DATA SHEET

Part No. T18RA50HSW
Article No. 120-05003
Type T18RA50



HellermannTyton's AT2000 is designed to use 18 lb. cable ties and will fasten bundles up to 3/4" diameter. Engineered specifically for automatic cable tie assembly, these ties are offered in varying material compositions and colors, so manufacturers can select the ties that meet the application requirements and industry best practices.

Material	Polyamide 6.6 heat stabilized (PA66HS)
Operating Temperature	-40°F to +257°F (-40°C to +125°C)
Flammability	UL 94 V-2
Halogen Free	Yes
UV Resistant	No
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	500
Carton Qty.	20000
Customs Number	3926909988

Length (imperial)	4.0 "
Length (metric)	4.8 mm
Max. Bundle Diameter (imperial)	0.79 "
Max. Bundle Diameter (metric)	20.0 mm
Min. Bundle Diameter (imperial)	0.03 "
Min. Bundle Diameter (metric)	0.7 mm
Min. Tensile Strength (imperial)	18 lbs
Min. Tensile Strength (metric)	80 N
Width (imperial)	0.1 "
Width (metric)	2.5 mm

