

TECHNICAL DATA SHEET

Part No. 120-05015
Article No. 120-05015
Type T18RA5000



HellermannTyton's AT2000 is designed to use 18 lb. cable ties and will fasten bundles up to 3/4" diameter. Engineered specifically for automatic cable tie assembly, these ties are offered in varying material compositions and colors, so manufacturers can select the ties that meet the application requirements and industry best practices.

Material	Polyamide 4.6 (PA46)
Operating Temperature	-40°F to +275°F (-40°C to +135°C)
Flammability	UL 94 V-2
Halogen Free	Yes
UV Resistant	No
Use Conditions	For Indoor Use Only
Color	Natural (NA)
Pkg. Qty.	5000
Carton Qty.	2
Customs Number	3926909988

Length (imperial)	4.0 "
Length (metric)	4.8 mm
Max. Bundle Diameter (imperial)	0.79 "
Max. Bundle Diameter (metric)	20.0 mm
Min. Bundle Diameter (imperial)	0.03 "
Min. Bundle Diameter (metric)	0.7 mm
Min. Tensile Strength (imperial)	18 lbs
Min. Tensile Strength (metric)	80 N
Width (imperial)	0.1 "
Width (metric)	2.5 mm

