

TECHNICAL DATA SHEET

Part No. 126-00041
Article No. 126-00041
Type T18RWPM



Wing design helps stabilize the tie in high vibration applications. One-piece mounting ties offer a complete solution by both bundling cable and simultaneously providing a mounting solution. HellermannTyton's one-piece mounting ties offer the ideal combination of high specification materials and superior design to suit the mounting and bundling needs of complex applications.

Material	Polyamide 6.6 (PA66)
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Flammability	UL 94 V-2
Plenum Rating	AH-2
UV Resistant	No
Use Conditions	For Indoor Use Only
Color	Natural (NA)
Pkg. Qty.	100
Carton Qty.	10000
Customs Number	3926909988

Fixation Method	Arrowhead
Height (imperial)	.23 "
Height (metric)	5.80 mm
Length (imperial)	4.5 "
Length (metric)	113.0 mm
Max. Bundle Diameter (imperial)	0.87 "
Max. Bundle Diameter (metric)	22.2 mm
Min. Tensile Strength (imperial)	18 lbs
Min. Tensile Strength (metric)	80 N
Mounting Hole Diameter (imperial)	0.19 - 0.22 "
Mounting Hole Diameter (metric)	4.8 - 5.6 mm
Panel Thickness (imperial)	0.06 - 0.13 "
Panel Thickness (metric)	1.52 - 3.2 mm
Thickness (imperial)	0.043 "
Thickness (metric)	1.1 mm
Width (imperial)	0.1 "
Width (metric)	2.5 mm

RoHS✓

