

TECHNICAL DATA SHEET

Part No. 126-00045
Article No. 126-00045
Type T50SSF



One-piece mounting ties offer a complete solution by both bundling cable and simultaneously providing a mounting solution. The arrowhead design of this push mount inserts easily and locks securely in place. HellermannTyton's one-piece mounting ties combine high-specification materials with superior design to deliver dependable performance in a range of applications.

Material	Polyamide 6.6 (PA66)
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Flammability	UL 94 V-2
UV Resistant	No
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	100
Carton Qty.	5000
Customs Number	3926909988

Fixation Method	Arrowhead
Height (imperial)	.30 "
Height (metric)	7.50 mm
Length (imperial)	6.25 "
Length (metric)	159.0 mm
Max. Bundle Diameter (imperial)	1.38 "
Max. Bundle Diameter (metric)	35.0 mm
Min. Tensile Strength (imperial)	50 lbs
Min. Tensile Strength (metric)	225 N
Mounting Hole Diameter (imperial)	0.25 - 0.28 "
Mounting Hole Diameter (metric)	6.4 - 7.1 mm
Panel Thickness (imperial)	0.04 - 0.14 "
Panel Thickness (metric)	1.0 - 3.56 mm
Width (imperial)	0.19 "
Width (metric)	4.7 mm

