

TECHNICAL DATA SHEET

Part No. 126-00065
Article No. 126-00065
Type T50SOSSFT6.5E-MS-MD



The arrowhead design of these ties offers a positive, low insertion force and a high extraction force. These ties feature a foam rubber seal which provides additional protection against moisture, dirt, and other impurities. One-piece mounting ties offer a complete solution by both bundling cable and at the same time providing a mounting solution. HellermannTyton's one-piece mounting ties offer the ideal combination of high specification materials and superior design to suit the mounting and bundling needs of complex applications.

Material	Polyamide 6.6 heat stabilized (PA66HS)
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Flammability	UL 94 V-2
UV Resistant	No
Use Conditions	For Indoor Use Only
Color	Natural (NA)
Pkg. Qty.	500
Carton Qty.	3000
Customs Number	3926909988

Fixation Method	Arrowhead
Height (imperial)	0.63 "
Length (imperial)	6.5 "
Length (metric)	163.0 mm
Max. Bundle Diameter (imperial)	1.38 "
Max. Bundle Diameter (metric)	35.0 mm
Min. Tensile Strength (imperial)	40 lbs
Min. Tensile Strength (metric)	180 N
Mounting Hole Diameter (imperial)	0.24 - 0.26 " (HEXAGONAL), 0.25 - 0.27 "
Mounting Hole Diameter (metric)	6.1 - 6.6 mm (hexagonal), 6.25 - 6.75 mm
Panel Thickness (imperial)	0.03 - 0.06 "
Panel Thickness (metric)	0.7 - 1.6 mm
Thickness (imperial)	0.05 "
Thickness (metric)	1.3 mm
Width (imperial)	0.18 "
Width (metric)	4.6 mm

RoHS