

TECHNICAL DATA SHEET

Part No. 126-00069
Article No. 126-00069
Type T50SSFM



Wing design helps stabilize the tie in high vibration applications. One-piece mounting ties offer a complete solution by both bundling cable and simultaneously providing a mounting solution. HellermannTyton's one-piece mounting ties offer the ideal combination of high specification materials and superior design to suit the mounting and bundling needs of complex applications.

Material	Polyamide 6.6 (PA66)
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Flammability	UL 94 V-2
UV Resistant	No
Use Conditions	For Indoor Use Only
Color	Natural (NA)
Pkg. Qty.	500
Carton Qty.	5000
Customs Number	3926909988

Fixation Method	Arrowhead
Height (imperial)	0.2 "
Height (metric)	5.6 mm
Length (imperial)	6.3 "
Length (metric)	160.0 mm
Max. Bundle Diameter (imperial)	1.38 "
Max. Bundle Diameter (metric)	35.0 mm
Min. Tensile Strength (imperial)	50 lbs
Min. Tensile Strength (metric)	225 N
Mounting Hole Diameter (imperial)	0.24 - 0.26 "
Mounting Hole Diameter (metric)	6.0 - 6.6 mm
Panel Thickness (imperial)	0.03 - 0.12 "
Panel Thickness (metric)	0.7 - 3.0 mm
Width (imperial)	0.18 "
Width (metric)	4.6 mm

RoHS