

TECHNICAL DATA SHEET

Part No. 126-00075
Article No. 126-00075
Type T50SOSKSFT5.4E



The low-profile push mount design provides an overall shortened length, which assists in limiting protrusion on the opposing side of application surfaces. The mount's rounded tip allows for a smoother surface in case of contact with surrounding components or hands. The dome provides firm, rattle-free performance and keeps out debris. One-piece mounting ties offer a complete solution by both bundling and mounting.

Material	Polyamide 6.6 heat stabilized (PA66HS)
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Flammability	UL 94 V-2
UV Resistant	No
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	500
Carton Qty.	6000
Customs Number	3926909988

Fixation Method	Arrowhead
Length (imperial)	6.0 "
Length (metric)	156.0 mm
Max. Bundle Diameter (imperial)	1.38 "
Max. Bundle Diameter (metric)	35.0 mm
Min. Tensile Strength (imperial)	50 lbs
Min. Tensile Strength (metric)	180 N
Mounting Hole Diameter (imperial)	0.20 - 0.22 "
Mounting Hole Diameter (metric)	5.2 - 5.6 mm
Panel Thickness (imperial)	0.03 - 0.05 "
Panel Thickness (metric)	0.7 - 1.3 mm
Width (imperial)	0.18 "
Width (metric)	4.6 mm

RoHS