

TECHNICAL DATA SHEET

Part No. 126-02300
Article No. 126-02300
Type T50SST5



The Domed Push Mount Tie provides a tight, rattle-free installation and acts as a seal to keep out dust and debris. One-piece mounting ties offer a complete solution by both bundling cable and at the same time providing a mounting solution.

Material	Polyamide 6.6 (PA66)
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Flammability	UL 94 V-2
UV Resistant	No
Use Conditions	For Indoor Use Only
Color	Natural (NA)
Pkg. Qty.	1000
Carton Qty.	5000
Customs Number	3926909988

Fixation Method	Arrowhead
Height (imperial)	0.4 "
Length (imperial)	7.0 "
Length (metric)	170.0 mm
Max. Bundle Diameter (imperial)	1.22 "
Max. Bundle Diameter (metric)	31.0 mm
Min. Tensile Strength (imperial)	50 lbs
Min. Tensile Strength (metric)	225 N
Mounting Hole Diameter (imperial)	0.24 - 0.26 "
Mounting Hole Diameter (metric)	6.1 - 6.5 mm
Panel Thickness (imperial)	0.03 - 0.06 "
Panel Thickness (metric)	0.7 - 1.5 mm
Thickness (imperial)	0.05 "
Thickness (metric)	1.2 mm
Width (imperial)	0.18 "
Width (metric)	4.6 mm

RoHS