

# TECHNICAL DATA SHEET

**Part No.** 133-00997  
**Article No.** 133-00997  
**Type** HC2E



HC Clamps separate multiple bundles and secure them to brackets or frame rails. Each mount has two pawls for easy pre-installation on a threaded fastener prior to securing with a mechanical fastener. HC Clamps have ribs that make them ideal for convoluted tubing, but they can also be used to separate separate bundles that aren't protected with convoluted tubing.

<b>Material</b>	Polyamide 6.6, high impact modified, glass-fiber reinforced (PA66HIRGF13)
<b>Operating Temperature</b>	-40°F to +257°F (-40°C to +125°C)
<b>UV Resistant</b>	No
<b>Use Conditions</b>	For Indoor and Outdoor Use
<b>Color</b>	Red (RD)
<b>Pkg. Qty.</b>	500
<b>Carton Qty.</b>	500
<b>Customs Number</b>	3926909988

<b>Height (imperial)</b>	1.38 "
<b>Height (metric)</b>	34.94 mm
<b>Length (imperial)</b>	2.747 "
<b>Length (metric)</b>	67.77 mm
<b>Max. Bundle Diameter (imperial)</b>	0.51 "
<b>Max. Bundle Diameter (metric)</b>	13.03 mm
<b>Mounting Hole Diameter (imperial)</b>	0.32 "
<b>Mounting Hole Diameter (metric)</b>	8.12 mm
<b>Width (imperial)</b>	1.1 "
<b>Width (metric)</b>	27.94 mm

RoHS