

TECHNICAL DATA SHEET

Part No. 133-00998
Article No. 133-00998
Type HC3A



HC Clamps separate multiple bundles and secure them to brackets or frame rails. Each mount has two pawls for easy pre-installation on a threaded fastener prior to securing with a mechanical fastener. HC Clamps have ribs that make them ideal for convoluted tubing, but they can also be used to separate separate bundles that aren't protected with convoluted tubing.

Material	Polyamide 6.6, high impact modified, glass-fiber reinforced (PA66HIRGF13)
Operating Temperature	-40°F to +257°F (-40°C to +125°C)
UV Resistant	No
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	500
Carton Qty.	500
Customs Number	3926909988

Height (imperial)	1.38 "
Height (metric)	34.94 mm
Length (imperial)	4.246 "
Length (metric)	107.86 mm
Max. Bundle Diameter (imperial)	0.96 "
Max. Bundle Diameter (metric)	24.3 mm
Mounting Hole Diameter (imperial)	0.32 "
Mounting Hole Diameter (metric)	8.12 mm
Width (imperial)	1.1 "
Width (metric)	27.94 mm

RoHS 