

TECHNICAL DATA SHEET

Part No. 133-01476
Article No. 133-01476
Type MINICHNLU



HellermannTyton Mini Channels provide protection and configurable routing in a cost-effective wire management solution. The variety of sizes and configurations enables engineers and installers to create optimum routing scenarios. Mini channels replace engineered channels that are costly to design and develop.

Material	Polypropylene 20% Talkum (PPTD20)
Operating Temperature	-40°F to +149°F (-40°C to +65°C)
Flammability	UL 94 HB
UV Resistant	No
Use Conditions	For Indoor Use Only
Color	Black (BK)
Pkg. Qty.	3000
Carton Qty.	3000
Customs Number	3926909988

Height (imperial)	1.18 "
Height (metric)	30.0 mm
Length (imperial)	1.97 "
Length (metric)	50.0 mm
Width (imperial)	0.31 "
Width (metric)	8.0 mm

