

TECHNICAL DATA SHEET

Part No. 133-01480
Article No. 133-01480
Type 45MINICHNL



HellermannTyton Mini Channels provide protection and configurable routing in a cost-effective wire management solution. The variety of sizes and configurations enables engineers and installers to create optimum routing scenarios. Mini channels replace engineered channels that are costly to design and develop.

Material	Polypropylene 20% Talkum (PPTD20)
Operating Temperature	-40°F to +149°F (-40°C to +65°C)
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant	No
Use Conditions	For Indoor Use Only
Color	Black (BK)
Pkg. Qty.	4000
Carton Qty.	4000
Customs Number	3926909988

Height (imperial)	0.39 "
Height (metric)	10.0 mm
Length (imperial)	2.05 "
Length (metric)	52.0 mm
Mounting Hole Diameter (metric)	6.1 - 6.9 mm
Width (imperial)	0.06 "
Width (metric)	10.0 mm

