

TECHNICAL DATA SHEET

Part No. 133-02835
Article No. 133-02835
Type T50SOSA6.5



One-piece mounting ties offer a complete solution by both bundling cable and simultaneously providing a mounting solution. Wing design helps stabilize the tie in high vibration applications. Mounting ties offer the ideal combination of high specification materials and superior design to suit the mounting and bundling needs of complex applications.

Material	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Use Conditions	For Indoor Use Only
Color	Gray (GY)
Pkg. Qty.	2400
Carton Qty.	2400
Customs Number	3926909988

Fixation Method	Arrowhead
Height (imperial)	0.039 "
Height (metric)	19.0 mm
Length (imperial)	5.83 "
Length (metric)	148.1 mm
Max. Bundle Diameter (imperial)	1.38 "
Max. Bundle Diameter (metric)	35.0 mm
Min. Tensile Strength (imperial)	50 lbs
Min. Tensile Strength (metric)	225 N
Mounting Hole Diameter (imperial)	0.24 - 0.26 ", 0.24 - 0.28 "
Mounting Hole Diameter (metric)	6.2 - 6.5 mm, 6.0 - 7.0 mm
Panel Thickness (imperial)	0.03 - 0.06 "
Panel Thickness (metric)	0.8 - 1.5 mm
Thickness (imperial)	0.05 "
Thickness (metric)	1.2 mm
Width (imperial)	0.19 "
Width (metric)	4.8 mm

RoHS ✓