

TECHNICAL DATA SHEET

Part No. 133-02836
Article No. 133-02836
Type T50ROSFT6.5



One-piece mounting ties offer a complete solution by both bundling cable and simultaneously providing a mounting solution. Wing design helps stabilize the tie in high vibration applications.

Material	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Use Conditions	For Indoor Use Only
Color	Gray (GY)
Pkg. Qty.	3000
Carton Qty.	3000
Customs Number	3926909988

Fixation Method	Fir tree for round holes
Height (imperial)	0.59 "
Height (metric)	15.1 mm
Length (imperial)	6.0 "
Length (metric)	151.7 mm
Max. Bundle Diameter (imperial)	1.97 "
Max. Bundle Diameter (metric)	50.0 mm
Min. Tensile Strength (imperial)	50 lbs
Min. Tensile Strength (metric)	222 N
Mounting Hole Diameter (imperial)	0.25 - 0.28 "
Mounting Hole Diameter (metric)	6.3 - 7.0 mm
Panel Thickness (imperial)	0.03 - 0.25 "
Panel Thickness (metric)	0.8 - 6.3 mm
Thickness (imperial)	0.05 "
Thickness (metric)	1.2 mm
Width (imperial)	0.19 "
Width (metric)	4.8 mm

RoHS